

CS9000-NH-HTEMP120V

Captures and kills harmful micro-particles for safer, cleaner air

Comfort Sentry[®] Air Clean9000




PRODUCT DETAILS

As part of a whole-home purification solution, the Comfort Sentry Air Clean 9000 reduces mold, germs, viruses, bacteria, fungi, and spores from your indoor air and within your HVAC system. Using a patented "dual" air cleaning process, the Air Clean 9000 both "captures" and "kills" harmful microparticles that can irritate asthma, allergies, and other ailments. This product sterilizes your indoor air, making it safer for you and your family.

- Removes up to 99% of allergens, molds, virus and bacteria
- Controls Odors
- Maintains system energy efficiency

FEATURES


- Patented "dual" air cleaning processes - captures & kills microparticles
- Optimum microparticle collection
- Natural, safe, electrical processes
- 4.5" Programmable color Touchscreen
- Simple maintenance
- Up to 99% efficient



This Product Controls

- 1
- 2
- 3
- 4

The EPA has ranked indoor air pollution among the top five environment dangers to the public.



APPLICATION

- Kills and controls germs, infectious agents and toxic gases
- Allergy relief
- Controls odors



PRODUCT SPECIFICATIONS

POWER REQUIRED	MODEL DESIGNATION	HIGH TEMP	REPLACEMENT CARTRIDGE	LCD OPTION	STATIC PRESSURE	FPM AIRFLOW	NOMINAL SIZE	ACTUAL SIZE
120 Volt	CS9000-NH-HTEMP120V	YES	TFI-AC-9000MC-1625	NO	.13/.17	300/400	16" X 25" X 7"	18.75" X 28" X 7.5"
120 Volt	CS9000-NH-TOUCH120V	NO	TFI-AC-9000MC-1625	YES	.13/.17	300/400	16" X 25" X 7"	18.75" X 28" X 7.5"





PRODUCT SCHEMATIC

1. Release the Lock Latch

2. Remove media cartridge



3. Insert replacement cartridge

4. Re-attach front cover panel



5. Lock In closed position

6. Reset notificatio timer



INSTALLATION NOTES

- 24 V low voltage connection
- High Temperature option, up to 220o Fahrenheit
- Snap in components allowing separate mounting of metal cabinet base for installation ease & versatility
- Touchscreen features annual service notification
- Vertical or horizontal mounting
- Fully reversible for left or right installation

SAFETY NOTES

- READ AND FOLLOW ALL INSTRUCTIONS.
- Always be sure the unit is unplugged during installation or service procedures.
- The ultraviolet light produced by the UV lamp is harmful to your eyes. Do not look directly at the lamp. Should it become necessary to view the lamp, use UV-protected sunglasses.

